



**Splice Connector**  
**T&B Catalog Number:**

54511  
 78621054511  
 Active

**UPC Number:**  
**Status:**  
**Description:**

Copper Two-Way Splice - Short Barrel for 3/0 AWG, 325/24, 2/0 Weld, Die Code 50 Orange

**Features**

Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.

**General**

Style	Two-Way Standard Barrel Splice
Material	Copper
Finish	Tin-Plated
Wire Size	3/0 AWG
Wire Size Flex	325/24 = 131kcmil, 2/0 Weld, 133/.0316, 259/.0227, 427/.0177
Die Color	Orange
Die Code	50

**Dimension Information**

A (inches)	1.75
E (inches)	.63

**Specifications**

Voltage Rating	600V
----------------	------

**Packaging**

T&B Order Multiple	10
T&B Inner Pack	10
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	7.1 lbs. per 100

**Application Support**

T&B Instruction Sheets	ta00676-tb2
------------------------	-------------

**Certifications**

RoHS Compliance	Yes
-----------------	-----

**Certifications**



File Nbr:  
 Y

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email:techsupport@tnb.com