



Disconnects
T&B Catalog Number:

RB14-250FP

UPC Number:

78621016981

Status:

Active

Description:

Insulated Nylon Piggy Back - 250 Series Disconnects For Wire Range 16-14 Length 0.87, Tab Size .250 x .032 , Blue

WEB_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

Designed for stacking applications.

General

Disconnect Type	Piggy Back - 250 Series
Insulation Type	Insulated Nylon
Terminal Series	RB
Material	Brass
Finish	Electro -Tin Plated
Color	Blue
Wire Range	16-14
Tab Size	.250 x .032

Dimension Information

Maximum Insulation (inches)	.163
Stock Thickness	.03
A (inches)	.87
B (inches)	.30
C (inches)	.43

Specifications

Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-2

Tooling

Tool Charts	Available on Website
Application Tools	WT112M
Recommended Tool	ERG4001, WT112M

Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	500
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	0.35 lbs. per 100
Alternate Package Qty	RB250P

Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E66716

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com