



## Splice Connector T&B Catalog Number:

54510

## UPC Number:

78621054510

## Status:

Active

## Description:

Copper Two-Way Splice - Short Barrel for 2/0 AWG, 275/24, 1/0 Weld, Die Code 45 Black

## Features

Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.

## General

Style	Two-Way Standard Barrel Splice
Material	Copper
Finish	Tin-Plated
Wire Size	2/0 AWG
Wire Size Flex	275/24 = 111 kcmil, 1/0 Weld, 427/.0155, 133/.0282
Die Color	Black
Die Code	45



## Dimension Information

A (inches)	1.75
E (inches)	.57

## Specifications

Voltage Rating	600V
----------------	------

## Packaging

T&B Order Multiple	10
T&B Inner Pack	10
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	6.44 lbs. per 100

## Application Support

T&B Instruction Sheets	ta00676-tb2
------------------------	-------------

## Certifications

RoHS Compliance	Yes
-----------------	-----

## Certifications



File Nbr:

Y

For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: techsupport@tnb.com