



## Liquidtight Flexible Metal Conduit Fittings

**T&B Catalog Number:**

5346

**UPC Number:**

78621005346

**Status:**

Active

**Description:**

1-1/2 Inch 45 degree malleable iron insulated liquidtight connector

### Features

Ability to install quickly with low torque effort

### Application

Used where flexible metal raceway is installed in outdoor or indoor locations where exposed to continuous or intermittent moisture.

To positively bond conduit to box or enclosure.

### General

Style	Insulated
Trade Size (inches)	1 1/2
Material	Malleable Iron
Finish	Electro Zinc Plated/Chromate Coating

### Dimension Information

Dimension A (inches)	2 23/32
Dimension B (inches)	3 3/8
Dimension C (inches)	13/16

### Specifications

3dmodel	Available on Website
---------	----------------------

### Accessories & Components

Wiremesh Grips for Liquidtight Fittings	WMG-LT6
---	---------

### Packaging

T&B Inner Pack	2
Package in Units	10
T&B Sold in UOM	Each
T&B Weight Per UOM	149.5 lbs. per 100

### Certifications

RoHS Compliance	Yes
-----------------	-----

### Certifications



File Nbr:

E 23018

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com