



Splice Connector T&B Catalog Number:

2A-18

UPC Number:

78621080001

Status:

Active

Description:

Non-Insulated Butt Splice Connector For Wire Range 22-18 Length .62
Diameter .12, Metallic

WEB_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

General

Insulation Type	Non-Insulated
Terminal Series	A
Material	Copper
Finish	Electro -Tin Plated
Color	Metallic
Wire Range	22-18

Dimension Information

Stock Thickness	.03
A (inches)	.62
B (inches)	.12

Specifications

Temperature Rating	150°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

Tooling

Tool Charts	Available on Website
Application Tools	WT110M, WT111M, WT112M, WT2000, ERG4002
Recommended Tool	ERG4002

Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	500
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	2.5 lbs. per 1000
Alternate Package Qty	AA2

Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:

E9809



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com