



Armored Cable/Flexible Metal Conduit Fittings

T&B Catalog Number:

304

UPC Number:

78621000304

Status:

Active

Description:

3/4 in. Tite-Bite® Connector, Malleable Iron.

Features

Easy to install with double grip saddle, connectors are completely salvageable.

Application

For use with Armored Cable and Flexible Metal Conduit.

To connect and effectively bond armored cable or flexible metal conduit to a box or an enclosure.

General

Trade Size (inches)

3/4

Material

Malleable Iron

Finish

Electro Zinc Plated

Dimension Information

Dimension A (inches)

1 7/8

Dimension B (inches)

1 11/16

Dimension C (inches)

1 7/32

Knockout Size (inches)

3/4

Cable Opening-Minimum (inches)

0.906

Cable Opening-Maximum (inches)

1.093

Specifications

3dmodel

Available on Website

Packaging

T&B Inner Pack

25

Package in Units

100

T&B Sold in UOM

Each

T&B Weight Per UOM

17.6 lbs. per 100

Notes

UL Listed for metal clad cable (MCI)

Certifications

RoHS Compliance

Yes

Certifications



File Nbr:

E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com