



Splice Connector T&B Catalog Number:

54808

UPC Number:

78621054808

Status:

Active

Description:

Copper Two-Way Splice - Long Barrel for 1 AWG, 150/24 Die Code 37
Green

Features

Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.

General

Style	Two-Way Long Barrel Splice
Material	Copper
Finish	Tin-Plated
Wire Size	#1 AWG
Wire Size Flex	150/24 = 60.5 kcmil, 175/24 = 70.6 kcmil
Die Color	Green
Die Code	37

Dimension Information

A (inches)	2.00
E (inches)	0.49

Specifications

Voltage Rating	600V
----------------	------

Packaging

T&B Inner Pack	20
Package in Units	200
T&B Sold in UOM	Each
T&B Weight Per UOM	4.85 lbs. per 100

Application Support

T&B Instruction Sheets	ta00674-tb2
------------------------	-------------

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:

Y

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com