

Standard Barrel Copper Lug

T&B Catalog Number:

54183

UPC Number:

78621054183

Status:

Active

Description:

Copper One-Hole Lug - Straight Standard Barrel - max 35KV, 350 kcmil Wire, 5/8" Bolt Size, Tin Plated with Inspection Hole, Red 71

General

Material	Copper
Finish	Tin Plated
Wire Size	350 kcmil
Number of Studs	1
Stud Size	5/8
Tongue Angle	Straight
Barrel Length	Standard
Barrel Shape	Standard
Tongue Width	Standard
Peep Hole	Y
Marking	Standard
Hole Shape	Round
Die Color	Red
Die Code	71

Dimension Information

A (inches)	3.21
B (inches)	1.58
C (inches)	1.36
D (inches)	0.18
E (inches)	0.93
F (inches)	5/8

Tooling

Connector & Tooling Chart	Available on Website
---------------------------	----------------------

Packaging

T&B Order Multiple	10
T&B Inner Pack	10
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	24.38 lbs. per 100

Application Support


T&B Instruction Sheets	ta00884-tb2
Product Overview	Available on Website

Notes

Dimensions given for reference only. Dimensions may vary up to .030.

Certifications

RoHS Compliance	Yes
-----------------	-----



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.

T&B Technical Support
MS 3B-50

Hours: 7AM - 6PM CDT
Monday-Friday

Memphis, TN 38125
www.tnb.com

8155 T&B Blvd.
Memphis, TN 38125

Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com