



Armored Cable/Flexible Metal Conduit Fittings

T&B Catalog Number:

UPC Number:

275

Status:

78621000275

Description:

Active

1 1/2 in. Malleable Iron Squeeze Connector-90 Degree.

Features

Cap lifts off by simply loosening screws part way, only two screws to tighten.

Application

For use with Armored Cable and Flexible Metal Conduit.

General

Trade Size (inches)

1 1/2

Material

Malleable Iron

Finish

Zinc Plate

Dimension Information

Dimension A (inches)

3 3/8

Dimension B (inches)

3 5/16

Dimension C (inches)

4

Knockout Size (inches)

1 1/2

Cable Opening-Minimum (inches)

1.625

Cable Opening-Maximum (inches)

1.875

Packaging

T&B Inner Pack

1

Package in Units

10

T&B Sold in UOM

Each

T&B Weight Per UOM

201.5 lbs. per 100

Notes

UL Listed for flexible metal conduit only.

Certifications

RoHS Compliance

No

Certifications

File Nbr:

E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com