



Liquidtight Flexible Cord & Cable Fittings

T&B Catalog Number:

2519

UPC Number:

78621002519

Status:

Active

Description:

3/8 in. straight steel liquidtight strain relief cord connector, cord range-.150-.300.

Application

Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

Meets Coast Guard CG293

General

Material Steel

Dimension Information

Hub Size (inches) 3/8
 Dimension A (inches) 31/32
 Dimension B (inches) 1 1/2
 Dimension C (inches) 15/32
 Cord Range (inches) .150-.300
 Throat Diameter (inches) 29/64

Specifications

3dmodel Available on Website
 Temperature Rating 105 C

Packaging

T&B Inner Pack 25
 Package in Units 100
 T&B Sold in UOM Each
 T&B Weight Per UOM 10.63 lbs. per 100

Application Support

Product Overview Available on Website
 Specifications Available on Website
 Portable Cord Selection Table Available on Website

Notes

Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
 E 13938

For further technical assistance, please contact us...

8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com