

Long Barrel Copper Lug T&B Catalog Number:

54876BE

UPC Number:


78621088273

Status:

Active

Description:

Copper Two-Hole Lug - Straight Long Barrel - max 35KV, 500 kcmil Wire, 1/2" Bolt Size, 1 3/4" Hole Spacing, Tin Plated Blind End, Brown 87



General

Material	Copper
Finish	Tin Plated
Wire Size	500 kcmil
Number of Studs	2
Stud Size	1/2
Bolt Hole Spacing	1 3/4
Tongue Angle	Straight
Barrel Length	Long
Barrel Shape	Standard
Tongue Width	Standard
Peep Hole	N
Marking	Standard
Hole Shape	Round
Die Color	Brown
Die Code	87

Dimension Information

A (inches)	5.953
B (inches)	2.984
C (inches)	1.609
D (inches)	.219
E (inches)	1.094
F (inches)	.5
G (inches)	1.75

Tooling

Connector & Tooling Chart	Available on Website
---------------------------	----------------------

Packaging

T&B Inner Pack	6
Package in Units	30
T&B Sold in UOM	Each
T&B Weight Per UOM	69.5 lbs. per 100

Application Support

T&B Instruction Sheets	ta01025-tb2
Product Overview	Available on Website

Notes

Dimensions given for reference only. Dimensions may vary up to .030.

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com