



## Liquidtight Flexible Cord & Cable Fittings

**T&B Catalog Number:**

2275

**UPC Number:**

78621002275

**Status:**

Active

**Description:**

1 in. 90 degree malleable iron liquidtight strain relief cord connector, cord range-.750-.875.

### Application

Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

Meets Coast Guard CG293

### General

Material Malleable Iron

### Dimension Information

Hub Size (inches)	1
Dimension A (inches)	1 11/16
Dimension B (inches)	2
Dimension C (inches)	13/16
Cord Range (inches)	.750-.875

### Specifications

3dmodel	Available on Website
Temperature Rating	105 C

### Packaging

T&B Inner Pack	5
Package in Units	25
T&B Sold in UOM	Each
T&B Weight Per UOM	48.81 lbs. per 100

### Application Support

Product Overview	Available on Website
Specifications	Available on Website
Portable Cord Selection Table	Available on Website

### Notes

Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

### Certifications

RoHS Compliance Yes

### Certifications



File Nbr:

E 13938

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289

