



Rigid/IMC Conduit Fittings

T&B Catalog Number:

1456

UPC Number:

78621001456

Status:

Active

Description:

2 in. Non-Metallic Knockout Plug, thermoplastic. For use with Rigid/IMC Conduit.

Application

To plug unused knockout openings in a box or enclosure.

General

| | |
|---------------------|---------------|
| Trade Size (inches) | 2 |
| Material | Thermoplastic |

Dimension Information

| | |
|----------------------|------|
| Dimension A (inches) | 2.74 |
| Dimension B (inches) | 0.57 |

Specifications

| | |
|---------|----------------------|
| 3dmodel | Available on Website |
|---------|----------------------|

Packaging

| | |
|--------------------|-------------------|
| T&B Order Multiple | 25 |
| T&B Inner Pack | 25 |
| Package in Units | 100 |
| T&B Sold in UOM | Each |
| T&B Weight Per UOM | 5.38 lbs. per 100 |

Certifications

| | |
|-----------------|-----|
| RoHS Compliance | Yes |
|-----------------|-----|

Certifications



File Nbr:

E 13938

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com