



Liquidtight Flexible Cord & Cable Fittings

T&B Catalog Number:

2673

UPC Number:

78621002673

Status:

Active

Description:

1/2 in. Black Beauty nylon straight liquidtight cord connector, cord range-.400 -.560.

Features

Hand tightens, no tools needed for assembly.

Segmented chuck provides high mechanical pullout performance, will not cut or damage cord jacket.

Application

To connect flexible cord to a box or enclosure and provide adequate strain relief.

Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC. Class I, Div 2; Class II, Div 1 & 2; Class III, Div 1 & 2; NEC 501-4(b), 502-4(a)(b), 503-3(a)(b)

Meets Coast Guard CG293

General

Material

Nylon

Dimension Information

Hub Size (inches)

1/2

Dimension A (inches)

2.6

Dimension B (inches)

1.27

Dimension C (inches)

0.60

Cord Range (inches)

.400-.560

Throat Diameter (inches)

0.55

Specifications

3dmodel

Available on Website

Temperature Rating

34 C - 105 C

Packaging

T&B Inner Pack

25

Package in Units

100

T&B Sold in UOM

Each

T&B Weight Per UOM

5.69 lbs. per 100

Application Support

T&B Instruction Sheets

ta01320-tb2

Product Overview

Available on Website

Portable Cord Selection Table

Available on Website

Notes

Remove sufficient outer covering of cable to permit conductors to pass thru connector body.

Certifications

RoHS Compliance

Yes

Certifications



File Nbr:
E 13938

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com