



Splice Connector T&B Catalog Number:

54008-TB
78621054008
Active

UPC Number:
Status:
Description:

Copper Two-Way Splice - Long Barrel for 1 AWG, Die Set 15CA37R
Green

Features

Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.

General



Style	Two-Way Long Barrel Splice
Material	Copper
Finish	Tin-Plated
Wire Size	#1 AWG
Strip Length (inches)	1 5#8
Die Color	Green
Die Set	15CA37R

Dimension Information

Strip Length (inches)	1 5#8
A (inches)	2.25
E (inches)	0.47

Specifications

Voltage Rating	600V
----------------	------

Tooling

Application Tools	13100A, TBM15I, TBM14M
-------------------	------------------------

Packaging

T&B Inner Pack	20
Package in Units	200
T&B Sold in UOM	Each
T&B Weight Per UOM	5.5 lbs. per 100

Notes

Cat. No. 15500-TB Die Adapter required for TBM15I Tool.

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
Y

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321

