



**Non-Metallic Sheathed Cable Conduit Fittings**

**T&B Catalog Number:**

3306

**UPC Number:**

78621003306

**Status:**

Active

**Description:**

1 1/2 Inch. Two Screw Connector, Malleable Iron-Electro Zinc Plated.

**Features**

Rounded cable grip and smooth bushing protect the cable sheath and wire insulation. Since saddle is threaded, screws do not travel or extend beyond the connector body as it is clamped to the cable. An extra lip on the saddle closes the unused part of the connector opening.

**Application**

To connect non-metallic sheathed cable and flexible cord to a box or an enclosure.

**General**

Material	Malleable Iron
Finish	Electro Zinc Plated

**Dimension Information**

Dimension A (inches)	2 5/32
Dimension B (inches)	2 21/32
Dimension C (inches)	1 29/32
Knockout Size (inches)	1 1/2
Cable Opening-Minimum (inches)	0.930
Cable Opening-Maximum (inches)	1.515

**Specifications**

3dmodel	Available on Website
---------	----------------------

**Packaging**

T&B Inner Pack	5
Package in Units	20
T&B Sold in UOM	Each
T&B Weight Per UOM	51 lbs. per 100

**Notes**

U.L. listed and CSA certified for the following single (1) of NM and NMC cable; (1) 3#4.

U.L. listed and CSA certified for the following Service Entrance Cables; GND, 3#3/0, 3#4/0, 2#3/0 + #1/0 GND, 2#4/0 + #2/0 GND.

**Certifications**

RoHS Compliance	Yes
-----------------	-----

**Certifications**



File Nbr:  
E 17583

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)