



## Liquidtight Flexible Cord & Cable Fittings T&B Catalog Number:

**UPC Number:** Status: **Description:** 

2556 78621002556 Active

1-1/4 in. straight malleable iron liquidtight strain relief cord connector, cord range-1.187-1.375.

Application

	O titable for use in boundary land titate where we
	Suitable for use in hazardous locations where gen- eral purpose equipment is specifically permitted by NEC 501-4(b).
	Meets Coast Guard CG293
General	
Material	Malleable Iron
Dimension Information	
Hub Size (inches)	1 1/4
Dimension A (inches)	2 11/32
Dimension B (inches)	2 1/2
Dimension C (inches)	13/16
Cord Range (inches)	1.187-1.375
Throat Diameter (inches)	1 1/4
Specifications	
3dmodel	Available on Website
Temperature Rating	105 C
Packaging	
T&B Inner Pack	5
Package in Units	25
T&B Sold in UOM	Each
T&B Weight Per UOM	78 lbs. per 100
Application Support	
. pp. eacher eachpert	
Product Overview	Available on Website
Specifications	Available on Website
Portable Cord Selection Table	Available on Website
Notes	
	Remove sufficient outer covering of cable to permit
	conductors to pass thru connector body.
Certifications	
RoHS Compliance	Yes
Certifications	
(HL)	
File Nbr	

File Nbr: E 13938

For further technical assistance, please contact us...

Thomas & Betts - USA 8155 T&B Blvd. Memphis, TN 38125

**T&B** Technical Support MS 3B-50 8155 T&B Blvd.

Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289



www.tnb.com

Memphis, TN 38125

Fax: (901) 252-1321 Email:techsupport@tnb.com