

## ETH-ADJSP-HD



Ajustable splice. Hot-dipped galvanized steel.



### General

Type:	Splices
Application:	Used to construct angles or bends with a radius
T&B UPC:	78621076309
T&B Status:	M
Special Features:	Tool required: 10 mm nut driver
Material:	Hot-dipped galvanized steel

### Packaging Information

Std pack:	25
-----------	----

### Dimension Information

Weight kg/ea:	0.06
Weight/Ea.:	0.13