



Splice Connector
T&B Catalog Number:

54508
 78621054508
 Active

UPC Number:
Status:
Description:

Copper Two-Way Splice - Short Barrel for 1 AWG, 150/24, 2 Weld, Die Code 37 Green

Features

Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.

General

Style	Two-Way Standard Barrel Splice
Material	Copper
Finish	Tin-Plated
Wire Size	#1 AWG
Wire Size Flex	150/24 = 60.5 kcmil, 175/24 = 70.6 kcmil, #2 Weld, 133/.0223
Die Color	Green
Die Code	37

Dimension Information

A (inches)	1.50
E (inches)	.47

Specifications

Voltage Rating	600V
----------------	------

Packaging

T&B Order Multiple	20
T&B Inner Pack	20
Package in Units	200
T&B Sold in UOM	Each
T&B Weight Per UOM	3.44 lbs. per 100


Application Support

T&B Instruction Sheets	ta00676-tb2
------------------------	-------------

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
 Y

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com

