

## Long Barrel Aluminum Lug T&B Catalog Number:

60116-TB

**UPC Number:**


78621060116

**Status:**

Active

**Description:**

Aluminum One-Hole Lug - Straight Long Barrel - max 35KV, #2 AWG Wire, 1/4" Bolt Size, Tin Plated Blind End, Pink 42



### General

Material	Aluminum
Finish	Tin Plated
Wire Size	#2 AWG
Number of Studs	1
Stud Size	1/4
Tongue Angle	Straight
Barrel Length	Long
Barrel Shape	Standard
Tongue Width	Standard
Peep Hole	N
Marking	Standard
Hole Shape	Round
Die Color	Pink
Die Code	42

### Specifications

Voltage Rating	600V to 35KV
----------------	--------------

### Tooling

Connector & Tooling Chart	Available on Website
---------------------------	----------------------

### Packaging

T&B Order Multiple	10
T&B Inner Pack	10
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	3 lbs. per 100

### Application Support

T&B Instruction Sheets	ta00880-tb2
Overview	Available on Website

### Notes

Dimensions given for reference only. Dimensions may vary up to .030.

### Certifications

RoHS Compliance	Yes
-----------------	-----

### Certifications



File Nbr:  
E9809

For further technical assistance, please contact us...

8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)