Thomas&Betts



Splice Connector T&B Catalog Number:

UPC Number: Status: **Description:**

RAA217 78621081796 Active

Expanded Insulated Vinyl Butt Splice Connector For Wire Range 22-18 Length 1.13 Diameter .23, Red WEB_USE

US Cutsheet PDF Catalog Link

http://www-public.tnb.com/contractor/docs/ stakon.pdf

T			(
Ļ		A	h
	Ц		Ī
t	8		N F

Features	
	In butt splices, the wires are butted together and
	crimped at each end of the splice. These splices
	are color-coded according to wire size.
General	
	Expanded Insulated Vinul
Insulation Type Terminal Series	Expanded Insulated Vinyl
Material	Copper
Finish	Electro -Tin Plated
Color	Red
	22-18
Wire Range 22-18 Dimension Information 22-18	
Dimension mormation	
Maximum Insulation (inches)	.155
Stock Thickness	.03
A (inches)	1.13
B (inches)	.23
Specifications	
Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0
Tooling	
Tool Charts	Available on Website
Application Tools	WT145C, WT2000, WT112M, ERG4001, ERG4003
Recommended Tool	ERG4001
Packaging	
T&B Order Multiple	1000
T&B Inner Pack	1000
Package in Units	10000
Package Type	Bulk
T&B Sold in UOM	Each
T&B Weight Per UOM	0.25 lbs. per 100
Application Support	
Overview	Available on Website
Wire Guide Tables	Available on Website
Certifications	
RoHS Compliance	Yes



Certifications

File Nbr:

E9809

For further technical assistance, please contact us...

T&B Technical Support MS 3B-50 8155 T&B Blvd. Memphis, TN 38125

(SP)

Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@thb.com

Thomas & Betts - USA 8155 T&B Blvd. Memphis, TN 38125 www.tnb.com