Thomas@Betts





RA1157

UPC Number: 78621081765 Active

Status:

Description:

Insulated Vinyl Fork Terminal For Wire Range 22-16 Stud Size #10, Red

WEB_USE

US Cutsheet PDF Catalog Link http://www-public.tnb.com/contractor/docs/

stakon.pdf

Features

These fork terminals have extra-long PVC insulation sleeve for protection and stress relief at wire's flex point. Brazed seam barrel is serrated for high pull-out value. Insulation is color-coded.

General



Maximum Insulation (inches)	.150	
Stock Thickness	.03	
A (inches)	.97	
B (inches)	.31	
C (inches)	.27	
M (inches)	.81	
Specifications		


Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

Tooling

Tool Charts Available on Website **Application Tools** WT145C, WT2000, WT112M, ERG4001, ERG4003

Application 10010	*** 100, *** 12000, *** 1 12m, 2100 1001, 2100 1000
Recommended Tool	ERG4001
Packaging	
T&B Order Multiple	1000
T&B Inner Pack	1000
Package in Units	5000
Package Type	Bulk
T&B Sold in UOM	Each
T&B Weight Per UOM	0.22 lbs. per 100
Alternate Package Qty	18RA-10F
Application Support	

Overview	Available on Website
Wire Guide Tables	Available on Website





Notes

Most terminals can be put on Mylar Tape for reel fed applications by adding the suffix M to the bulk catalog numbers.

Certifications

RoHS Compliance

Yes

Certifications





File Nbr: E9809

For further technical assistance, please contact us...

T&B Technical Support MS 3B-50 8155 T&B Blvd. Memphis, TN 38125 Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@tnb.com

Thomas & Betts - USA 8155 T&B Blvd. Memphis, TN 38125 www.tnb.com