



## Armored Cable/Flexible Metal Conduit Fittings

**T&B Catalog Number:**

314

**UPC Number:**

78621000314

**Status:**

Active

**Description:**

2 1/2 in. Tite-Bite Connector, Malleable Iron-Electro Zinc Plated

### Features

Easy to install with double grip saddle, connectors are completely salvageable.

### Application

For use with Armored Cable and Flexible Metal Conduit.

To connect and effectively bond armored cable or flexible metal conduit to a box or an enclosure.

### General

Trade Size (inches)

2 1/2

Material

Malleable Iron

Finish

Electro Zinc Plated

### Dimension Information

Dimension A (inches)

3 1/2

Dimension B (inches)

3 1/8

Dimension C (inches)

2 1/4

Knockout Size (inches)

2

Cable Opening-Minimum (inches)

2.812

Cable Opening-Maximum (inches)

3.062

### Specifications

3dmodel

Available on Website

### Packaging

T&B Inner Pack

1

Package in Units

5

T&B Sold in UOM

Each

T&B Weight Per UOM

284 lbs. per 100

### Notes

UL Listed for flexible metal conduit only.

### Certifications

RoHS Compliance

No

### Certifications



File Nbr:

E 23018

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com