

## Liquidtight Flexible Cord & Cable Fittings T&B Catalog Number:

2557

**UPC Number:** 78621002557

Status: Active

**Description:** 

1-1/4 in. straight malleable iron liquidtight strain relief cord connector, cord range-1.375-1.485.

range-1.375-1.485.	
Application	
	Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).
_	Meets Coast Guard CG293
General	
Material	Malleable Iron
Dimension Information	
Hub Size (inches)	1 1/4
Dimension A (inches)	2 11/32
Dimension B (inches)	2 1/2
Dimension C (inches)	13/16
Cord Range (inches)	1.375-1.485
Throat Diameter (inches)	1 1/4
Specifications	
3dmodel	Available on Website
Temperature Rating	105 C
Packaging	
T&B Inner Pack	5
Package in Units	25
T&B Sold in UOM	Each
T&B Weight Per UOM	70.81 lbs. per 100
Application Support	
Product Overview	Available on Website
Specifications	Available on Website
Portable Cord Selection Table	Available on Website
Notes	
	Remove sufficient outer covering of cable to permit conductors to pass thru connector body.
Certifications	
RoHS Compliance	Yes
Certifications	



File Nbr: E 13938

For further technical assistance, please contact us...

Hours: 7AM - 6PM CDT

Monday-Friday Phone: (888) 862-3289

T&B Technical Support MS 3B-50 8155 T&B Blvd.



www.tnb.com Memphis, TN 38125

Fax: (901) 252-1321 Email:techsupport@tnb.com