



**Disconnects**  
**T&B Catalog Number:**

B14-110F  
 78621080333  
 Active

**UPC Number:**  
**Status:**  
**Description:**

Non-Insulated Female - 110 Series Disconnects For Wire Range 16-14 Length 0.59, Metallic

**WEB\_USE**

US Cutsheet PDF Catalog Link <http://www-public.tnb.com/contractor/docs/stakon.pdf>

**General**

Disconnect Type	Female - 110 Series
Insulation Type	Non-Insulated
Terminal Series	B
Material	Brass
Finish	Electro -Tin Plated
Color	Metallic
Wire Range	16-14
Tab Size	.110 x .032

**Dimension Information**

Stock Thickness	.03
A (inches)	.59
B (inches)	.15

**Specifications**

Temperature Rating	150°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0

**Tooling**

Tool Charts	Available on Website
Recommended Tool	WT111M

**Packaging**

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	500
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	1.25 lbs. per 1000
Alternate Package Qty	B10TB

**Application Support**

Wire Guide Tables	Available on Website
-------------------	----------------------

**Certifications**

RoHS Compliance	Yes
-----------------	-----

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)