

T&B® Fittings



T&B Catalog Number: LTC038GY
UPC Number: 78621088075
Description: 3/8" PVC Commercial Grade Type B non-metallic liquidtight conduit; color-Gray.

Status: Active

Features

Also available in Black, Orange or Blue.

General

Material	PVC
Color	Gray
Conduit Size (inches)	3/8

Dimension Information

I.D. - Minimum (inches)	.484
I.D. - Maximum (inches)	.504
O.D. - Minimum (inches)	.690
O.D. - Maximum (inches)	.710

Packaging

T&B Order Multiple	100
Package in Units	100
T&B Sold in UOM	Feet
T&B Weight Per UOM	12.7 lbs. per 100

Application Support

MSDS Number	MSDS-0023-TB2
XTRAFLEX System Specifications	Available on Website

Notes

*Note	Commercial Grade U.L. Listed
**Note	80° C temperature rated; UV resistant.

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E 95745

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com