



Motor Lead Disconnect

T&B Catalog Number:

MD40M-3

UPC Number:

78621084061

Status:

Active

Description:

KUBE Male (One Load) Copper Motor Pigtail Disconnect for Wire Size 4/0 AWG, Body Size 3, Die Color Purple

Features

Fast, snap-together assembly offers maximum labor savings. Not need for nuts, bolts and washers or insulating tape - simply slide on reusable boot.

Quick disconnect - no knife cutting of melted tape, eliminating the risk of accidental cutting of wire insulation, resulting motor downtime and installer exposure. Meets or exceeds electrical and mechanical performance of bolted connections.

General

Style	Male (One Load)
Material	Copper
Finish	Tin-Plated
Wire Size	4/0 AWG
Strip Length (inches)	3/4
Die Color	Purple
Die Code	54
Body Size	3
Boot Insulation	MDBOOT3

Dimension Information

Strip Length (inches)	3/4
A (inches)	.88
B (inches)	.88
C (inches)	1.81
D (inches)	1.75
E (inches)	.88
F (inches)	.500

Specifications

Voltage Rating	600V
----------------	------

Tooling

Application Tools	TBM6, TBM6S, TBM5, TBM5S, TBM8, TBM8S
-------------------	---------------------------------------

Packaging

T&B Order Multiple	3
T&B Inner Pack	3
Package in Units	30
T&B Sold in UOM	Each
T&B Weight Per UOM	34.69 lbs. per 100

Application Support

T&B Instruction Sheets	ta00220-tb2
------------------------	-------------

Notes

Always use the same body size when selecting male and female disconnects. Use insulating boots

matching the disconnect body size. To protect the connection from moisture and dirt, use sealing compound catalog number MDBOOT-SEAL.

Certifications

RoHS Compliance Yes

Certifications



File Nbr:

Y

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com