



Disconnects T&B Catalog Number:

UPC Number:
Status:
Description:

RA2577F
78621089443
Active

Insulated Nylon Female - 250 Series Disconnects For Wire Range 22-18
Length 0.8, Tab Size .250 x .032 , Red

WEB_USE

US Cutsheet PDF Catalog Link <http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

Unique construction of the female disconnect offers long-term dependability. Brazed seam serrated barrel provides maximum tensile strength.

General

Disconnect Type	Female - 250 Series
Insulation Type	Insulated Nylon
Terminal Series	RA
Material	Brass
Finish	Electro -Tin Plated
Color	Red
Wire Range	22-18
Tab Size	.250 x .032

Dimension Information

Maximum Insulation (inches)	.170
A (inches)	.80
B (inches)	.71

Specifications

Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-2

Tooling

Tool Charts	Available on Website
Application Tools	WT145C, WT2000, WT112M, ERG4001, ERG4003
Recommended Tool	ERG4001

Packaging

T&B Order Multiple	500
T&B Inner Pack	500
Package in Units	5000
Package Type	Bulk
T&B Sold in UOM	Each
T&B Weight Per UOM	0.44 lbs. per 100
Alternate Package Qty	RA18250A

Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E66716

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com