



Locking Fork Terminal T&B Catalog Number:

UPC Number:

RC10-8FL
78621088756

Status:

Active

Description:

Insulated Nylon Locking Fork Terminal For Wire Range 12-10 Stud Size #8, Yellow


WEB_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

Locking fork terminals have a specially designed tongue that lets them go on like a fork and stay on like a ring.



General

Insulation Type	Insulated Nylon
Terminal Series	RC
Material	Copper
Finish	Electro -Tin Plated
Color	Yellow
Wire Range	12-10
Stud Size	#8

Dimension Information

Maximum Insulation (inches)	.210
Stock Thickness	.04
A (inches)	1.00
B (inches)	.37
C (inches)	.27
M (inches)	.81

Specifications

Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-2

Tooling

Tool Charts	Available on Website
Application Tools	ERG4001, ERG4003, WT145C, WT2000, WT112M, WT145A
Recommended Tool	ERG4001

Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	250
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	0.63 lbs. per 1000
Alternate Package Qty	RC2213

Application Support

Overview	Available on Website
Wire Guide Tables	Available on Website

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com