



Liquidtight Flexible Metal Conduit Fittings

T&B Catalog Number:

5352GR

UPC Number:

78621090008

Status:

Active

Description:

1/2 Inch external bonding liquidtight insulated connector flexible metal conduit fitting, 90 Degree Angle, with Revolver? lug, with tin-plated copper alloy lug for AWG #14-#2 ground wire, for use in wet locations, 25 pieces

Features

Ability to install quickly with low torque effort

Application

To positively bond conduit to box or enclosure

General

Trade Size (inches)	1/2
Material	Malleable Iron
Finish	Electro Zinc Plated/Chromate Coating
Ground Wire	14-8

Dimension Information

Dimension A (inches)	1 3/8
Dimension B (inches)	1 7/16
Dimension C (inches)	9/16

Specifications

3dmodel	Available on Website
---------	----------------------

Packaging

T&B Inner Pack	25
Package in Units	50
T&B Sold in UOM	Each
T&B Weight Per UOM	31 lbs. per 100

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:

E 3060

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com