PHYSICAL INFRASTRUCTURE SYSTEMS

B. Copper Systems

C. Fiber Optic Systems

D. Power over Ethernet

E. Zone Cabling

F. Wireless

G. Outlets

H. Media Distribution

I. Physical Infrastructure Management

J. Overhead & Underfloor Routing

K. Surface Raceway

L. Cabinets, Racks & Cable Management

M. Grounding & Bonding

N. Industrial

0. Labeling & Identification

P. Cable Management Accessories

> Q. Index

GP6™ PLUS Category 6 High Density Kits

- Exceed ANSI/TIA-568-C.2 Category 6 standard
- Ideal for use in cross-connects and consolidation point applications
- Provides pre-packaged components necessary for termination
- Kit includes required quantity of bases and 4-pair connecting blocks, label holders and labels
- · Highly visible color-coded wiring slots ease wiring



GPKBW144Y



GPKBW432Y

Part Number	Part Description	Std. Pkg. Qty.	Ctn.
GPKBW144Y	144-pair (36-port) Category 6 high-density punchdown field termination kit with legs.	1	10
GPKBW432Y	432-pair (108-port) Category 6 high-density punchdown field termination kit with legs.	1	10

Cable requirement: terminates most 22-26 AWG solid or stranded IWC wire with a 0.050" (1.27mm) max o.d., either PVC or plenum rated.

Termination tool available on page B.79 of SA-NCCB51.

To ensure optimal performance, Panduit recommends use with other Panduit Category 6 PLUS components. Can be clearly identified with labels found on page B.76 of SA-NCCB51.



GP6™ PLUS Category 6 Standard Density Kits

- Exceed ANSI/TIA-568-C.2 Category 6 standard
- Ideal for use in cross-connects and consolidation point applications
- Provide pre-packaged components necessary for termination
- Kit includes required quantity of bases and 4-pair connecting blocks, label holders and labels
- Highly visible color-coded wiring slots ease wiring



GPKBW24Y



GPKBW72Y

Part Number	Part Description	Std. Pkg. Qty.	Ctn.
GPKBW24Y	96-pair (24-port) Category 6 punchdown base field termination kit with legs.	1	10
GPKBW72Y	288-pair (72-port) Category 6 punchdown base field termination kit with legs.	1	10

Cable requirement: terminates most 22 – 26 AWG solid or stranded IWC wire with a 0.050" (1.27mm) max o.d., either PVC or plenum rated.

Termination tool available on page B.79 of SA-NCCB51.

To ensure optimal performance, Panduit recommends use with other Panduit Category 6 PLUS components. Can be clearly identified with labels found on page B.76 of SA-NCCB51.