




Panduit® Type NNC Halogen-Free Metric Wiring Duct

- Material: Halogen-free modified polyphenylene oxide (mPPO) material as verified with IEC 60754-2 test method (test on gases evolved during combustion of electric cables)
- UL recognized continuous use temperature: 203°F (95°C)
- UL 94 flammability rating of V-0

- Conforms with NFPA 79-2007 section 13.3.1 requirement for flame retardant material
- Provided with DIN 43 659 mounting holes
- Metric sizing and finger progression
- Duct and cover packaged together in two meter lengths



Multiple slot restrictors present with 75mm and greater duct wall height.

| Base and Cover Part Number | Duct Size (W x H)* | | Slot Width | | Replacement Cover Part Number | Base and Cover Ctn. Qty. (m) | Replacement Cover Ctn. Qty. (m) |
|----------------------------|--------------------|-------------|------------|------|-------------------------------|------------------------------|---------------------------------|
| | mm | In. | In. | mm | | | |
| NNC25X25LG2 | 24.6 x 23.6 | .97 x .93 | .39 | 10.0 | NC25LG2 | 20 | 20 |
| NNC25X37LG2 | 24.6 x 35.8 | .97 x 1.41 | .39 | 10.0 | NC25LG2 | 20 | 20 |
| NNC25X50LG2 | 24.6 x 47.8 | .97 x 1.88 | .39 | 10.0 | NC25LG2 | 20 | 20 |
| NNC25X75LG2 | 24.6 x 72.4 | .97 x 2.85 | .39 | 10.0 | NC25LG2 | 20 | 20 |
| NNC37X37LG2 | 37.1 x 35.8 | 1.46 x 1.41 | .39 | 10.0 | NC37LG2 | 20 | 20 |
| NNC37X50LG2 | 37.1 x 47.8 | 1.46 x 1.88 | .39 | 10.0 | NC37LG2 | 20 | 20 |
| NNC37X75LG2 | 37.1 x 72.4 | 1.46 x 2.85 | .39 | 10.0 | NC37LG2 | 20 | 20 |
| NNC50X50LG2 | 49.5 x 47.8 | 1.95 x 1.88 | .39 | 10.0 | NC50LG2 | 20 | 20 |
| NNC50X75LG2 | 49.5 x 72.4 | 1.95 x 2.85 | .39 | 10.0 | NC50LG2 | 10 | 20 |
| NNC50X100LG2 | 49.5 x 97.8 | 1.95 x 3.85 | .39 | 10.0 | NC50LG2 | 10 | 20 |
| NNC75X75LG2 | 74.7 x 72.4 | 2.94 x 2.85 | .39 | 10.0 | NC75LG2 | 10 | 20 |
| NNC100X50LG2 | 99.6 x 47.8 | 3.92 x 1.88 | .39 | 10.0 | NC100LG2 | 10 | 20 |
| NNC100X75LG2 | 99.6 x 72.4 | 3.92 x 2.85 | .39 | 10.0 | NC100LG2 | 10 | 20 |
| NNC100X100LG2 | 99.6 x 97.8 | 3.92 x 3.85 | .39 | 10.0 | NC100LG2 | 10 | 20 |

Available in LG (Light Gray) and WH (White).


Do not allow cutting, tapping, or cleaning fluids that contain hydrocarbons to come in contact with type NNC wiring duct as it will cause stress cracking. See page C1.49 for a list of chemicals to avoid.

*"H" dimension includes duct and cover.

Panduit® Type NNC Divider Wall

- NNC solid divider wall can be mounted inside NNC and NE wiring duct to create multiple channels
- Material: Halogen-free modified polyphenylene oxide (mPPO)

- Simply install the divider wall base when mounting the duct and snap the divider wall onto mounting base, DB-C



| Part Number | Length (m) | For Nominal Duct Height (mm) | Std. Pkg. Qty. | Std. Ctn. Qty. (m) |
|-------------|------------|------------------------------|----------------|--------------------|
| NNC50DWH2 | 2 | 50 | 2 | 40 |
| NNC75DWH2 | 2 | 75 | 2 | 40 |

Available in WH (White) color only.

NOTE: Must be used with mounting base DB-C (see page C1.26), which is sold separately. Install mounting bases to the duct channel, locate within 2" of each divider wall end and at least every 12" along the length.

A. System Overview

B1. Cable Ties

B2. Cable Accessories

B3. Stainless Steel Ties

C1. Wiring Duct

C2. Surface Raceway

C3. Abrasion Protection

C4. Cable Management

D1. Terminals

D2. Power Connectors

D3. Grounding Connectors

E1. Labeling Systems

E2. Labels

E3. Pre-Printed & Write-On Markers

E4. Permanent Identification

E5. Lockout/Tagout & Safety Solutions

F. Index