



EXTRA HEAVY-DUTY SPEC. 347VAC TOGGLE SWITCH BACK & SIDE WIRE, LIGHT ALMOND

PS372030LA | [Pass & Seymour](#)

FEATURES & BENEFITS

3Way Canadian Toggle Switch, 20A 347VAC, Back & Side Wire, Light Almond



- External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.
- Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.
- Cam controls fast "make" and positive "break" to minimize arcing.
- Heavy-duty bumper pads for quiet operation.
- High strength thermoplastic polycarbonate toggle.
- Back body made of glass-reinforced nylon.
- Locking support provides resistance to face and back body separation.
- Oversized silver alloy contacts for long life and better heat dissipation.
- Grounding terminal is standard.
- Shallow design for ease of installation.
- Strap nickel-plated steel with integral ground.
- Auto-ground clip assures positive ground.
- For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

SPECIFICATIONS

GENERAL INFO

Color: Light Almond
Duty: Extra Heavy Duty

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: C22.2 111
CSA Standard: Yes
UN SPSC: 39121507

DIMENSIONS

Depth (US): 1.073"
Height (US): 3.531"
Width (US): 1.320"

TECHNICAL INFORMATION

Amps: 20A
Volts: 347VAC
Volts (AC): 347
Grade Type: Specification

COUNTRY OF ORIGIN

Country Of Origin: MEXICO