B. Copper Systems

C. Fiber

Optic

Systems

D. Power

over Ethernet

E. Zone Cabling

F. Wireless

G. Outlets

H. Media

Distribution

Grounding Strip Kits

- Bonds up to 45 RU per rack
- EIA Universal mounting hole pattern



Threaded Rail Kit



Cage Nut Rail Kit

Part Number	Part Description	Std. Pkg. Qty.
Grounding Strip	Kits for Threaded Rail Fasteners	
RGS134-1Y	Grounding strip; 78.65" (2m) length; .67" (17mm) width; .05" (1.27mm) thickness; provided with .16 oz. (5cc) of antioxidant, one grounding sticker and three each #12-24 x 1/2" and M6 x 12mm thread-forming screws.	1
RGS134-10-1Y	Ten grounding strips; 78.65" (2m) length; .67" (17mm) width; .05" (1.27mm) thickness; provided with .16 oz. (5cc) of antioxidant, ten grounding stickers and 30 each #12-24 x 1/2" and M6 x 12mm thread-forming screws.	1
Grounding Strip	Kits for Cage Nut Rail Fasteners	
RGS134B-1	Grounding strip; 78.70" (2m) length; .67" (17mm) width; .05" (1.27mm) thickness; provided with .16 oz. (5cc) of antioxidant, one grounding sticker, three cage nut bonding studs, eight #12-24 bonding nuts and three strip clips.	1
RGS134B-10-1	Ten grounding strips; 78.70" (2m) length; .67" (17mm) width; .05" (1.27mm) thickness; provided with .16 oz. (5cc) of antioxidant, ten grounding stickers, 30 cage nut bonding studs, 80 #12-24 bonding nuts and 30 strip clips.	1

grounding requirements

· Engineered to comply with US and International

l. Physical Infrastructure

Infrastructure Management

J. Overhead & Underfloor Routing

> K. Surface Raceway

L. Cabinets, Racks & Cable

Racks & Cable Management

M. Grounding & Bonding

N. Industrial

0. Labeling & Identification

P. Cable Management Accessories

> Q. Index

	Grounding	Busbar	Kits
LISTED CERTIFIED			

- Provide the common grounding point within the cabinet
- Optimized for installation on 19" racks or cabinets that meet EIA-310-D
- Can be positioned anywhere on the rack or cabinet



RGRB19U

Part Number	Part Description	Std. Pkg. Qty.
Grounding Busb	ar Kits for Threaded Rail Fasteners	
RGRB19Y	Grounding busbar; 19" (483mm) length; tin-plated; fourteen holes arranged for flexibility in mounting; provided with two each #12-24 x 1/2" and M6 x 12mm thread-forming screws.	1
RGRB19U	Grounding busbar; 19" (483mm) length; tin-plated; twenty holes arranged for flexibility in mounting with twenty #12-24 x 1/2" hex head screws installed; mounting hole sets have $5/8$ " (15.9mm) spacing; provided with two each #12-24 x 1/2", M6 x 12mm thread-forming screws, and two #12 flat washers for mounting.	1
Grounding Busb	ar Kit for Cage Nut Rail Fasteners	
RGRB19CN	Grounding busbar; 19" (483mm) length; tin-plated; twenty holes arranged for flexibility in mounting with twenty #12-24 x 1/2" hex head screws installed; mounting hole sets have 5/8" (15.9mm) spacing; provided with two cage nut bonding studs and four #12-24 bonding nuts.	1

quick and easy installation

grounding requirements

· Available pre-assembled with twenty mounting screws for

· Engineered to comply with US and International