Arlington



Zero to 90™ **Connectors**

For use with non-metallic liquid-tight conduit, type B only. Produced from UV rated plastic for long outdoor life.







CATALOG NUMBER	UPC/DCI/NAED MFG #018997			UNIT PKG			DIM B	DIM C	DIM D
NMLT5090	06240	1/2	1/2	10	50	2.765	1.945	2.324	2.387
NMLT7590	06260	3/4	3/4	10	50	3.540	2.590	3.250	2.820

PATENTED.









COSTS THE SAME "REGULAR" 90° FITTING!

Installation Instructions



Arlington's no-spin ferrule allows the Zero to 90 connector to be secured to the conduit while fully assembled. To install, simply loosen the tightening nut and screw onto conduit. A positive liquid-tight seal is formed by the pressure sensitive internal gland as the nut is tightened. The sealing ring assures a liquid-tight seal between the fitting and box.

Adjusts for ALL ANGLES... from 0° to 90°!

To adjust the angle simply loosen the center nut, twist to the correct angle, and retighten.



Tel: (800) 233-4717 Email: sales@aifittings.com www.aifittings.com Fax: (570) 562-0646