

Intercom Room Unit, Indoor, Light Almond

IC1004-LA



The Broadcast Intercom Room Unit offers a simple interface for communication with other intercom stations in the home. The modern, adjustable backlit keypad makes it simple to communicate in low-light conditions. In addition to paging, the user can monitor other units from anywhere in the house.

features & benefits

- Specially filtered to help reduce electrical interference noise.
- Simple RJ45 plug design for easy installation and troubleshooting.
- Trims with a standard decorator wall plate (included).
- Page, monitor and do not disturb features.
- Multi-level volume control.
- Modern backlit keypad.

specifications

General Info

Cable Type: Cat 5
Color: Light Almond
Connection Type: 110 Punchdown
Product Series: inQUIRE 1000
Type: Inquire Room Unit
Style: Decorator

Listing Agencies/Third Party Information

FCC Standard: Yes
UN SPS C: 43221525

Dimensions

Depth Metric: 4.5 cm
Depth U S: 1.8"
Height Metric: 11.9 cm
Height U S: 4.69"
Width Metric: 12.1 cm
Width U S: 4.75 in

Cord Information

Cord Length U S: 325 Foot home-run

Pinning:

- | | |
|-----------------|-------------------------|
| 1. Green/White | Audio Direction Control |
| 2. Green | Monitor Button |
| 3. Orange/White | Power (12V) |
| 4. Blue | Ground |
| 5. Blue/White | Audio In |
| 6. Orange | Audio Out |
| 7. Brown/White | Talk Button |
| 8. Brown | Door Button |

Technical Information

Humidity: 90% Relative Humidity (Non-Condensing)
Operating Temperature Celsius: 0°C to 55°C
Operating Temperature Fahrenheit: 32°F to 131°F
Power Requirements: Powered by Intercom Module
Supported Standards: FCC PART 15 B