JUNO°

UNDERCABINET LIGHTING

Project: Fixture Type: Location: Contact/Phone:

PRO-SFRIFS XFNON

20W - 12-volt Xenon Lamps

UPX109, UPX214, UPX322 and UPX430

PRODUCT DESCRIPTION

The Pro-Series Xenon modular series with integral electronic transformer operates 12-volt halogen lamps to deliver the best color rendering with maximum light output and lamp life. The efficient operation of low voltage lamps, along with a unique housing/reflector system, reduces mounting surface temperatures well below what is typical for xenon undercabinet fixtures. Pro-Series Xenon fixtures are optimized for fast permanent installation, mounting either flush to the rear backsplash or to the front lip of cabinetry to suit project conditions and homeowner preference.

PRODUCT SPECIFICATIONS

Lamp 20W-12-volt xenon bi-pin high output lamps supplied with fixture • Projected 10,000 hour life based on actual operating voltage in fixture.

Transformer Integral Electronic 120 to 12-volt step down transformer is accessible for maintenance without having to

Housing Extruded aluminum • Designer white, black, brushed bronze or brushed silver finish.

Reflector Specular aluminum reflector behind each lamp.

Diffuser Clear prismatic tempered glass lens for maximum light transmission • Reverse-angled to minimize preceived brightness • Captive lens has hinged design for tool-less relamping • Spring-loaded retention bar prevents lens from accidently being bumped

Switch Convenient integral Hi/Lo/Off rocker switch.

Dimming For best results use dimmer specifically designed for use with electronic low voltage transformers.

Labels UL Listed.

INSTALLATION

UPX series fixtures optimized with a center rear wiring access compartment and push-in 3-wire electrical connectors for quick electrical connection without having to open the fixture or remove the lens. Rear wiring access compartment covers provided with push-in connector for non-metallic cable and knockout for feed thru wiring capability. Multiple off-center knockouts provided in two, three and four lamp fixtures. Die-cast fitting for 3/8" flexible metal conduit supplied in a hardware pack. Fixtures may be mounted flush to the backsplash or up against the front lip of the cabinetry using captive external mounting screws.

Portable To install as a portable fixture, use the 3-wire grounded cord & plug (ULH-CP sold separately).

Optional Direct Wire Optional direct wire module (ULH-DWM sold separately) facilitates code-compliant installation of fixture at front edge of cabinetry. Supplied with 36" field-shortenable jumper cord to bring power to either end of the fixture.

Electrically Connecting Multiple Fixtures Up to 10 fixtures may be electrically joined together using either the straight joiner connector supplied with each fixture or the optional JC3 jumper cords. See accessories table for lengths and finishes.

PRO-SERIES XENON 5 MINUTE DIRECT-WIRE INSTALLATION



Step 1 Attach supply wires to rear access cover. wires to fixture leads REV-4/10




Step 2 Connect supply



Step 3 Mount fixture to cabinet bottom using using push-in connectors. captive mounting screws.

DIMENSIONS





ENGINEERING DATA

	UPX109	UPX214	UPX322	UPX430
Total input power (watts)	20	40	60	80
Total Operating AMPS	.17	.34	.50	.70
Power Factor	.99	.99	.99	.99

Maximum cabinet bottom contact temperature: less than 60° C.

PRODUCT CODES

Catalog Number	Finish	Overall Length	Lamp
UPX109-BL	Black	9 1/2"	1-20W
UPX109-BZ	Brushed Bronze	9 1/2"	1-20W
UPX109-SL	Brushed Silver	9 1/2"	1-20W
UPX109-WH	Designer White	9 1/2"	1-20W
UPX214-BL	Black	14"	2-20W
UPX214-BZ	Brushed Bronze	14"	2-20W
UPX214-SL	Brushed Silver	14"	2-20W
UPX214-WH	Designer White	14"	2-20W
UPX322-BL	Black	22"	3-20W
UPX322-BZ	Brushed Bronze	22"	3-20W
UPX322-SL	Brushed Silver	22"	3-20W
UPX322-WH	Designer White	22"	3-20W
UPX430-BL	Black	30"	4-20W
UPX430-BZ	Brushed Bronze	30"	4-20W
UPX430-SL	Brushed Silver	30"	4-20W
UPX430-WH	Designer White	30"	4-20W

ACCESSORIES

Description				
8" Jumper Cord				
17" Jumper Cord				
26" Jumper Cord				
3/8" Miniature Die-Cast Electrical Connector				
3-Wire Grounded Cord & Plug				
Direct Wire Module				
12V 20W Bi-Pin Xenon High Output Lamp				



UNDERCABINET LIGHTING


PRO-SERIES XENON

20W - 12-volt Xenon Lamps

UPX109, UPX214, UPX322 and UPX430

LIGHTING APPLICATION DATA

FOOTCANDLES ON HORIZONTAL WORK SURFACE



			Footcandles			
Cat #	Lamp	*Beam Width	A	В	С	D
UPX 109	(1) 20-watt Xenon	21 "	9	31	28	35
UPX214	(2) 20-watt Xenon	23"	15	53	48	54
UPX322	(3) 20-watt Xenon	31 "	24	72	65	62
UPX430	(4) 20-watt Xenon	36"	23	75	69	64

^{*}Beam width defined as 50% of maximum footcandles

Rear wall reflectance 50% Counter Surface Reflectance 20%

