JUNO°

| Project: | |
|----------------|--|
| Fixture Type: | |
| Location: | |
| Contact/Phone: | |

4" MINIATURE UNIVERSAL TC NEW CONSTRUCTION HOUSING

INCANDESCENT LAMPS

TC1

PRODUCT DESCRIPTION

TC New Construction Housing design for use in non-insulated areas • If installed where insulation is present, the insulation must be pulled back 3" from all sides of the TC housing.

PRODUCT SPECIFICATIONS

Lamp Lamp ratings based on trim selected - see reverse side.

Socket Detachable medium base porcelain with nickel-plated copper screw shell.

Trims Trim selection shown on reverse side.

Labels U.L. listed for through-branch wiring, damp locations and IP • Product thermally protected against improper use of lamps or insulation • Union made • UL Listed/CSA certified • Trim No. 11, 12, 4101, 4102 and 4181 are wet location approved for covered ceiling applications • Trims 14, 17 are wet location approved for covered ceiling applications, when used with outdoor rated lamps.

Testing All reports are based on published industry procedures; field performance may differ from laboratory performance.

Product specifications subject to change without notice.

INSTALLATION


Real Nail 3 Bar Hangers Telescoping Real Nail® 3 system covered under Patent D552,969 permits quick placement of housing anywhere within 24" O.C. joists or suspended ceilings • Integral T-bar notch and clip secures housing in suspended ceiling grid – no accessory clips required • 24" expansion stop allows quick placement of fixture in standard grid spacing • Bars scored in two locations for fast, clean breaking, allowing housing installation in tight applications • Bars captive to mounting frame • Edgemounted for extra strength • Captive bugle-headed ring shank nail for quick one-step installation and easy removal with claw hammer for fixture relocation • Quick-Loc slot (location identified on the mounting frame) and oversized locking set screw lock fixture in position • Bar hanger foot contoured to align to bottom of construction joist • Alternate mounting holes included.


Junction Box Pre-wired junction box provided with (5) ½" and (1) ¾" knockouts, (4) Non-metallic sheathed cable connectors and ground wire, U.L. listed/CSA certified for through-branch wiring, maximum 8 No. 12 AWG 90° C branch circuit conductors (4 in, 4 out) • Junction box provided with removable access plates • Knockouts equipped with pryout slots.

Mounting Frame 22-gauge die-formed galvanized steel mounting frame • 9%" L x 6%" W, (excluding bar hangers)
• Rough-in section (junction box, mounting frame, housing and bar hangers) fully assembled for ease of installation.

Housing TC housing, 22-gauge galvanized steel • Housing is vertically adjustable to accommodate up to a 1¹/₄″ ceiling thickness.

DIMENSIONS





4 1/2" CEILING CUTOUT

ACCESSORIES

| Catalog No. | Description | | |
|-------------|---|--|--|
| 4TSA | Torsion Spring Adapter (for original style housing) | | |
| GU10-WHIP | GU10 Socket Whip | | |

To order, specify catalog number

PRODUCT CODES

| Catalog Number | Input Voltage | Lamp Rating (max.) | | |
|----------------|---------------|--|--|--|
| TC1 | 120V | R14/R16/R20/PAR16/PAR20 (See reverse for max. trim rating) | | |



4" MINIATURE UNIVERSAL TC NEW CONSTRUCTION HOUSING

INCANDESCENT LAMPS

TC1

ROUND TRIMS/LAMPS

| | Cat. No. | Description | Max. Lamp Rating | | Cat. No. | Description | Max. Lamp Rating |
|-----------|---|--|---|-------|--|---|---|
| | 13-WH | 2" Pinhole with Integral Shield | 50W PAR20/50W R20 | | 16-WH | Scoop Wall Wash with higher inner shield | 40W R14/40W R16 intermediate screw base |
| | 14B-WH ◆◆ 14B-SC ◆◆ 14B-ABZ ◆◆ | Black Baffle Black Baffle Black Baffle | 50W PAR20/50W R20 | | 446-WH PAR16. | Scoop Adjustable | 50W MR16, 50W |
| | 14B-BL ♦♦ 14W-WH ♦♦ | Black Baffle White Baffle | | | TAKTO, | | 50W ES16 GU10 (Requires GU10-WHIP) |
| | 17C-WH ◆◆ 17G-WH ◆◆ 17B-WH ◆◆ 17PT-SC ◆◆ | Cone - Clear Alzak® Cone - Gold Alzak® Cone - Black Alzak® Cone - Pewter Alzak® | 50W PAR20/50W R20 | | 4101-WH ◆ 4101-SC ◆ 4101-ABZ ◆ | Beveled Dome Shower Beveled Dome Shower Beveled Dome Shower | 50W PAR/50W R20 |
| | | Cone - Gloss White Cone - Haze Cone - Wheat Haze Cone - Wheat Haze | | | 4102-WH ♦ 4102-SC ♦ 4102-ABZ ♦ | Beveled Shower Beveled Shower Beveled Shower | 50W PAR/50W R20 |
| | 10-WH 10-BL 10-SC | Push-In Flush Gimbal Ring Push-In Flush Gimbal Ring Push-In Flush Gimbal Ring | 50W PAR20/ 75W ES20 GU10 (Requires GU10-WHIP) | | 4103FROST-WH 4103FROST-SC | Beveled Cylinder Beveled Cylinder | 50W PAR/50W R20 |
| | 10-ABZ 18-WH | Push-In Flush Gimbal Ring Mini Eyeball | 60W PAR16, 40W R16 | | 4104HZ-SC 4104WHZ-ABZ | Beveled Cone Beveled Cone | 50W PAR/50W R20 |
| | 18-SC 19-WH | Mini Eyeball Mini Eyeball | 40W R14/40W R16 | | 4150MESH-SC | Cylinder | 50W PAR/50W R20 |
| | ., | Will Eyebali | intermediate screw base | | l | | |
| | 440-WH 440-BL | Flush Gimbal Ring Flush Gimbal Ring | 50W MR16, 50W PAR16, 50W ES16 GU10 | | 4180FROST | Solid Glass Collar (torsion spring attachment) | 50W PAR/50W R20 |
| | 440-SC 440-ABZ | Flush Gimbal Ring Flush Gimbal Ring (New tighter gap, uses 2" optical media) | (Requires GU10-WHIP) | | 4181CLEAR ◆ | All Glass Shower (torsion spring attachment) | 50W PAR/50W R20 |
| | 445-WH | Slot Aperture Downlight or Adjustable | 50W MR16, 50W PAR16, | SQUAR | E TRIMS/LAMP | 5 | |
| | | g | 50W ES16 GU10 (Requires GU10-WHIP) | | Cat. No. | Description | Max. Lamp Rating |
| | 448-WH 448-SC | Eyeball with Black Baffle Eyeball with Black Baffle | 50W MR16, 50W PAR16, 50W ES16 GU10 (Requires GU10-WHIP) | | 17SQ-HZ-WH ◆◆ 7 17SQ-W-WH ◆◆ 17SQ-B-WH ◆◆ 17SQ-WHZ-WH ◆◆ | Square Downlight | 50W PAR20, 30W R20 |
| | 11-WH ◆ | Drop Opal | 50W PAR20/50W R20 | | 7 13SQ-WH | Square Pinhole | 50W PAR20, 50W R20 |
| | 12W-WH ◆ 12W-SC ◆ 12W-ABZ ◆ | Shower Trim, frosted perimter lens Shower Trim, frosted perimter lens Shower Trim, frosted perimter lens | 50W PAR20/50W R20 | [10] | 7 440SQ-WH 440SQ-BL | Square Flush Gimbal | 50W MR16 120V GU10 Base (Requires GU10-WHIP) 35* Vertical Adjustment |
| Tri | | Classic Aged Bronze, BL - Black, GP - Polycarbonate material shower trim), | | | 7 12SQ-W-WH ◆ | Square Frosted Lens with Clear Center | 50W PAR20, 50W R20 |
| SC Ala | C - Satin Chrome, S zak is a registered | SL - Silver, WH - White. I trademark of Alcoa Corp. | | ~ | GU10-WHIP | GU10 Socket Whip | |

Note: In Canada when insulation is present, Type IC fixtures must be used.

- ◆ UL Listed for use in wet location.
- ◆◆ UL Listed for use in wet location with outdoor rated lamp.

