G1.2.0

IC22

JUNO

Project:

Fixture Type:

Location:

Contact/Phone:

PRODUCT DESCRIPTION

IC Air-Loc® Housing • Energy efficient, sealed housing • Can be completely covered with insulation • When used with Air-Loc Gasket (see accessories), stops infiltration and exfiltration of air, reducing heating and cooling costs • Trims shown with Air-Loc symbol IRCO do not require a gasket.

PRODUCT SPECIFICATIONS

Lamp Lamp ratings based on trim selected-see reverse.

Socket Medium base porcelain with nickel-plated copper screw shell • Adjustable socket plate and detachable socket with snap-in springs to accommodate various lamp and trim combinations
Socket plate secured at two points for consistent, straight lamp positioning.

Trims Trim selection shown on reverse.

Labels U.L. listed for through-branch wiring, damp locations and IP • Product thermally protected against improper use of lamps • UL Listed/CSA certified • Trims 239, 241 and 242 are wet location approved for covered ceiling applications • Trims 28, 29 are wet location approved for covered ceiling applications, when used with outdoor rated lamps.

Testing All reports are based on published industry procedures; field performance may differ from laboratory performance.

Product specifications subject to change without notice.

INSTALLATION

Real Nail 3 Bar Hangers Telescoping, patent-pending Real Nail 3 system permits quick placement of housing anywhere within 24" O.C. joists or suspended ceilings • Integral T-bar notch and clip secures housing in suspended ceiling grid – no accessory clips required • 24" expansion stop allows quick placement of fixture in standard grid spacing • Bars scored in two locations for fast, clean breaking, allowing housing installation in tight applications • Bars captive to mounting frame • Edge-mounted for extra strength • Captive bugle-headed ring shank nail for quick onestep installation and easy removal with claw hammer for fixture relocation • Quick-Loc slot (location identified on the mounting frame) and oversized locking set screw lock fixture in position • Bar hanger foot contoured to align to bottom of construction joist

• Alternate mounting holes included.

Junction Box Pre-wired junction box provided with (5) ½" and (1) ¾" knockouts, (4) Non-metallic sheathed cable connectors and ground wire, U.L. listed/CSA certified for through-branch wiring, maximum 8 No. 12 AWG 90° C branch circuit conductors (4 in, 4 out) • Junction box provided with removable access plates • Knockouts equipped with pryout slots.


Mounting Frame 22-gauge die-formed galvanized steel mounting frame • Rough-in section (junction box, mounting frame, housing and bar hangers) fully assembled for ease of installation
Sight lines embossed on mounting frame to allow for easy viewing when aligning fixtures.


Housing IC housing, .032" aluminum sealed for Air-Loc Compliance • Housing is vertically adjustable to accommodate up to a 1" ceiling thickness.

IC HOUSING

6" ECONOMY UNIVERSAL

DIMENSIONS





6 7/8" CEILING CUTOUT

ACCESSORIES

Catalog No.	Description	
ALG6	Air-Loc Gasket	

To order, specify catalog number.



Catalog Number	Input Voltage	Lamp Rating (max.)
IC22	120V	A19/BR30/BR40/PAR16/PAR20/PAR30/PAR30L/PAR38/R20 (See reverse for max. trim rating)

PRODUCT CODES

G1.2.0

6" ECONOMY UNIVERSAL IC HOUSING

INCANDESCENT LAMPS

1022

	TRIMS/LA	MPS					IC22	
	Cat. No.	Description	Max. Lamp Rating		Cat. No.	Description	Max. Lamp Rating	
**	24B-WH 24B-SC 24B-ABZ	Conical Black Baffle Conical Black Baffle Conical Black Baffle	50W PAR30, 75W PAR30L, 65W BR30		248W-WH	R20 Eyeball in White Baffle	50W PAR20/R20	
	248-8L 24W-WH	Conical Black Baffle Conical White Baffle		\bigcirc	249B-WH 249W-WH	BR30 Eyeball in Black Baffle BR30 Eyeball in White Baffle	75W PAR3OL, 65W BR3	
**	25B-WH 25B-SC 25B-ABZ 25B-BL	Straight Black Baffle Straight Black Baffle Straight Black Baffle Straight Black Baffle	50W PAR30, 65W BR30	**	264B-WH 264W-WH	PAR30 Adjustable - Black Baffle PAR30 Adjustable - White Baffle	50W PAR30	
IR-LOC 🔲	25W-WH	Straight White Baffle		**	267C-WH 267G-WH 267B-WH	PAR30 Adjustable - Clear Alzak® PAR30 Adjustable - Gold Alzak® PAR30 Adjustable - Black Alzak®	50W PAR30	
	28B-WH ♦♦ 28W-WH ♦♦	Conical Black Baffle Conical White Baffle	60W A19, 65W BR30, 75W PAR30/30L, 90W PAR38, 90W BR40		267HZ-WH 267WHZ-WH	PAR30 Adjustable - Haze PAR30 Adjustable - Wheat Haze		
	29C-WH ♦♦ 29W-WH ♦♦	Deep Cone Clear Cone Deep Cone White Cone	60W A19, 65W BR30, 75W PAR30/30L, 90W PAR38, 90W BR40		XR30101WH XR30101BL XR30101GP XR30101SL	AVIO Square Gimbal Ring - White AVIO Square Gimbal Ring - Black AVIO Square Gimbal Ring - Graphite AVIO Square Gimbal Ring - Silver	75W PAR30	
	27C-WH 27G-WH 27B-WH	Conical Cone in Clear Alzak® Conical Cone in Gold Alzak® Conical Cone in Black Alzak®	50W PAR30, 75W PAR30L, 65W BR30		239-WH ♦	Frosted Lens	40W A19	
**	27PT-SC 27W-WH 27HZ-WH 27WHZ-WH	Conical Cone in Pewter Alzak® Conical Cone in Gloss White Conical Cone in Haze Conical Cone in Wheat Haze			241-WH ♦ 241-PW ♦	Drop Opal with Reflector Shower/Closet Light	40W A19	
4IR-LOC	27WHZ-ABZ 244B-WH	Conical Cone in Wheat Haze Conical Black Baffle	75W PAR3OL, 60W PAR3O,		242-WH ♦ 242-SC ♦ 242-ABZ ♦	Shower Trim, Frosted Lens with Clear Center	45W PAR38	
AIR-LOC)	244W-WH 247C-WH	Conical White Baffle Cone - Clear Alzak®	65W BR30 75W PAR30L, 65W BR30,		9324-SC	Luminous Disc	50W PAR30, 65W BR3 75W PAR30	
**	247G-WH 247B-WH 247HZ-WH 247WHZ-WH	Cone - Gold Alzak® Cone - Black Alzak® Cone - Haze	75W PAR30		9702	Luminous Collar	50W PAR30, 65W BR3 75W PAR30L	
	250-WH 250-SC 250-ABZ	Open Frame Open Frame Open Frame	65W BR30		9024W-WH	White Octagonal w/White Baffle	50W PAR30, 65W BR3 75W PAR30	
\bigcirc	252-WH	Regressed Open Frame	75W R/BR30		9524-SC	Chrome Band	65W BR30, 50W PAR3 75W PAR30L	
\bigcirc	231C-WH 231G-WH 231W-WH	Multiplier - Clear Alzak® Multiplier - Gold Alzak® Multiplier - Gloss White	60W A19	Trim Size: 7%" O.D. (except Cat. Nos. 228, 229, 241, 9024, - 8" O.D., Cat. No. 9702 - 7¾" O.D.). Trim Finish: ABZ - Classic Aged Bronze, BL - Black, GP - Graphite, PW - Plastic White (Polycarbonate material shower trim), SC - Satin Chrome, SL - Silver, WH - White. Alzak is a registered trademark of Alcoa Corp. Note: In Canada when insulation is present, Type IC fixtures must be used.				
	226B-WH 226W-WH	Black Cylinder w/Black Baffle White Cylinder w/White Baffle	60W PAR16					
	228-WH	R20 Regressed Eyeball	50W PAR20/R20	JUNO IC housings meet IECC Energy Code requirements per ASTM E283. Air-Loc® rated trims are pre-gasketed for minimum air leakage with IC housing				
	229-WH 229-SC	BR30 Regressed Eyeball BR30 Regressed Eyeball	75W PAR3OL, 65W BR30		for use in wet loc d for use in wet lo	ation. ocation with outdoor rated lamp.		
	229-ABZ 229-BL	BR30 Regressed Eyeball BR30 Regressed Eyeball				mpatible with 24, 25, 27, 244,		
		Endo Regressed Eyebuil			64, 267 trims.			



1300 S. Wolf Road • Des Plaines, IL 60018 • Phone (847) 827-9880 • Fax (847) 827-2925
 Juno Lisenting Group
 220 Chrysler Drive
 Brampton, Ontario
 Canada L6S 6B6
 Phone (905)
 792-7335
 Fax (905)
 792-0064

 by Schneider Fleetric
 Visit us at www.junolightinggroup.com
 Printed in U.S.A. ©2009 Juno Lighting
 Printed in U.S.A. ©2009 Juno Lighting, LLC.