



TRILIGHT LAMPS provide 3 intensities of light, adapting to your lighting needs.



Order code	Description	Watts (W)	Base	Volts (V)	Finish/Colour	Average life at 120 V (hrs)	Filament	Lumens at 120 V (lm)	Case qty
A21									
MOL : 5 7/16 in. (135 mm) LCL : 3 27/32 in. (98 mm)									
10500	30/100A21/F/4M/130V/STD	30 70 100	E26d	130	Frost	4 000	CC-8 CC-8	280 800 1 080	120
50152	30/100A21/WH/4M/130V/STD	30 70 100	E26d	130	White	4 000	CC-8 CC-8	230 760 990	120
52103	50/100/150A21/CP/4M/130V/STD	50 100 150	E26d	130	Ceramic pink	4 000	2C-6	N/A	25
50117	50/150A21/WH/4M/130V/STD	50 100 150	E26d	130	White	4 000	CC-8 CC-8	520 1 200 1 720	120
10486	50/150A21/F/4M/130V/STD	50 100 150	E26d	130	Frost	4 000	CC-8 CC-8	440 1 045 1 485	24
50516	50/150A21/WH/2M/120V/STD BLX	50 100 150	E26d	120	White	2 000	CC-8 CC-8	580 1 300 1 900	120
51159	50/250A21/WH/2M/120V/STD	50 200 250	E26d	120	White	2 000	CC-8 CC-8	400 2 200 2 600	120
50955	50/150A21/F/N/5M/120V/STD	50 100 150	E26	120	Frost	5 000	CC-8 CC-8	520 1 200 1 720	24
PS25									
MOL : 6 13/16 in. (176 mm) LCL : 5 1/2 in. (128 mm)									
51123	100/300/PS25/WH/E39/130V/STD	100 200 300	E39d	130	White	2 500	CC-6 CC-6	910 1 815 2 725	24

Trilight Lamps