


TracJack Stylistics Frame, three-port, Electrical Ivory

OR-41900017-13



features & benefits

TracJack Stylistics Plastic Duplex Frame accepts three front-loading TracJack modules in the rectangular electrical mounting footprint of a GFCI outlet. It is compatible with many cable delivery systems that can house electrical duplex outlets

- **Matches rectangular electrical outlet (GFI) footprint:** Supports use with electrical delivery system.
- **Field configurable with TracJacks:** Design or site flexibility for new or retrofit.
- **Supports TracJack footprint:** Broad offering of connector options.
- **Front load and access:** Connector access without removing plate.
- **Choice of colors:** Compatible with many environments.

specifications

General Info

Color: Electrical Ivory
Footprint: TracJack
Number Of Ports: 3
Product Series: Clarity
Type: Plates and Boxes

Assembly/Installation Information

Mounting Hardware Included: #6-32*25 mm Screw, Binding Head (2 ea)

Listing Agencies/Third Party Information

CUL Listing No: E131600
UL Listing No: E131600

UL Standard: Yes

Construction Information

Component1: Plastic TracJack Mounting Frame
Material1: High Impact Thermoplastic ABS 94V-0

Dimensions

Height Metric: 107.70 mm
Height U S: 4.24"
Width Metric: 45.97 mm

Buy American Act Compliance

Country of Origin: TAIWAN
Buy American Act Status: Trade Agreement Act Compliant