

# TracJack Module F Connector F/F, Black

OR-63700006-00



TracJack Module provides a single F-connector coupler F/F with under .2dB of insertion loss at 2GHz (1/3 the loss of standard models). TracJack is a versatile single jack solution in a front-load footprint which allows a choice of up to six jacks/connectors to fit in a single gang plate

## features & benefits

- F Connector coupler F/F
- Front removable
- Standard TracJack footprint

## specifications

### General Info

Color: Black  
Footprint: TracJack  
Number Of Ports: 2  
Product Series: TracJack  
Type: Video

### Listing Agencies/Third Party Information

CUL Listing No: E131600  
UL Listing No: E131600

### Construction Information

Component1: Plastic Series II Housing

Component2: F-Connector female/female coupler  
Material1: High Impact Thermoplastic ABS 94V-0  
Material2: Feed-through, RG6/59 (G-F81TN)

### **Dimensions**

Depth Metric: 14.48 mm  
Height Metric: 23.37 mm  
Height U S: 0.92"  
Width Metric: 18.54 mm

### **Technical Information**

Equipment Type: F Conn Coax

### **Buy American Act Compliance**

Country of Origin: MALAYSIA  
Buy American Act Status: Exception  
Notes: Contact Customer Support for Buy American Act options