

Multi-Conductor Unshielded Cable

Low Voltage Thermostat CSA CMG

Conductors: Solid Bare Copper
Insulation: PVC
Jacket: Brown PVC, (Other colors available).
Construction: Conductors cabled except where noted. (Flat items are parallel conductors).
Temperature Rating: 60°C
Color Code Chart: 11
Operating Voltage: 30 Volts
Applications: Thermostat controls, door bells, security systems and other low voltage remote control systems where voltage does not exceed 30 volts.
Approvals: CSA LVT CMG FT4



TEVELEC NUMBER	No. of Conds.	AWG Size	Stranding	Nominal Insulation	Nominal Jacket	Nominal O.D.	Weight Lbs/1000'
T2149	2 Flat	18	Solid	.015	.030	.143 X .213	26
T2150	2	18	Solid	.015	.030	.213	26
T2151	3	18	Solid	.015	.030	.225	33
T2152	4	18	Solid	.015	.030	.232	40
T2153	5	18	Solid	.015	.030	.243	51
T2154	6	18	Solid	.015	.030	.261	58
T2156	8	18	Solid	.015	.030	.292	81
T2158	10	18	Solid	.015	.030	.320	100
T2170	2 Flat	16	Solid	.015	.030	.166 X .224	48
T2173	4	16	Solid	.015	.030	.258	61