

Clarity 5E Modular Patch Cord, 3', white

OR-MC5E03-09



Clarity 5E Modular Patch Cord, 3', white

features & benefits



- ETL third party tested and verified to TIA/EIA 568B.2 Category 5e component specifications
- Each cord is factory tested
- Center tuned technology
- Paralign 2 pair-positioning technology
- Snagless design
- Icon compatibility
- Premium conductor cordage
- Compatible with both T568A and T568B wiring
- Improved signal to noise ratio

specifications

General Info

Cable Type: Four-pair stranded UTP non-plenum

Color Cable Jacket: White

Termination: 8-Pos Mod

Typical Applications: 10Base-T, 100Base-TX, 1000Base-T, 1000Base-TX, 155 Mb/s ATM, 1 Gb/s ATM (CB1G)

Product Series: Clarity

Type: Patch Cords and Cables

Listing Agencies/Third Party Information

ETL Listing No: COC 5e PATCH CORD

FCC Standard: Yes

Construction Information

Component1: Cable

Component2: Eight-position plug assembly

Component3: Modular plug IDC contacts

Component4: Paralign 2 pair segregation and strain relief

Finish Plating3: 50 Micro inch elective gold plating over nickel

Material1: 24 AWG bare copper stranded conductors, PVC insulation, PVC jacket

Material2: Polycarbonate plug housing and conductor positioning sled

Material3: Phosphor-bronze contacts

Material4: Molded Polypropylene Copolymer

Dimensions

Diameter Metric: 7.1 mm

Diameter U S: 0.28"

Length Metric: 0.91 m

Cord Information

Connector Type End One: Plug, HSG, eight-contact, RJ45, high performance

Connector Type End Two: Plug, HSG, eight-contact, RJ45, high performance

Jacket Color: White

Jacket Rating: CM

Cord Length U S: 3'

Min Bend Radius: 1.00"

Pinning: Straight 1-1, 2-2, 3-3, etc.

Technical Information

Category Rating: Cat5e

Ohm Value: 100 Ohm

Performance Rating: Cat5e

Sort Termination: 3

Wire Gauge: 24 AWG

Buy American Act Compliance

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant