

General Information

Extended Product Type:	OT200U03
Product ID:	1SCA022723R0220
EAN:	6417019232645
Catalog Description:	OT200U03 switch-disconnector
Long Description:	3-pole, front operated, base mounted non-fusible disconnect switch, handle and shaft are not included, terminal bolt kit included

Categories

Products » Low Voltage Products and Systems » Switches » Switch Disconnectors

Ordering

Minimum Order Quantity:	1 piece
Customs Tariff Number:	85365080

Popular Downloads

Data Sheet, Technical Information: [1SCC301020C0201](#)

Dimensions

Product Net Width:	170 mm 6.7 in
Product Net Height:	170 mm 6.7 in
Product Net Depth:	70 mm 2.8 in
Product Net Weight:	1.577 kg

Technical

Rated Operational Current AC-22A (I _e):	(500 V) 250 A (380 ... 415 V) 250 A (690 V) 250 A
Rated Operational Current AC-23A (I _e):	(380 ... 415 V) 250 A (500 V) 250 A (690 V) 250 A
Rated Operational Power AC-23A (P _e):	(380 ... 415 V) 110 kW (500 V) 132 kW (690 V) 200 kW
Rated Impulse Withstand Voltage (U _{imp}):	12 kV
Rated Insulation Voltage (U _i):	1000 V
Rated Operational Voltage:	1000 V
Rated Short-Circuit Making Capacity (I _{cm}):	(690 V AC) 30 kA
Rated Short-time Withstand Current (I _{cw}):	for 1 s 8 kiloampere rms
Power Loss:	at Rated Operating Conditions per Pole 6.5 W
Pollution Degree:	3
Handle Type:	Handle and shaft not included
Switches Operating Mechanism:	Mechanism at the End of the Switch 03 (Left Side)
Distance Between Phases:	Standard
Position of Line Terminals:	Top In - Bottom Out Bottom In - Top Out
Operating Mode:	Front operated
Standards:	IEC 60947-3, UL 98 / CSA C22.2 NO.4
Special Functions:	No
Mounting Type:	Base mounting
Number of Poles:	3
Terminal Type:	Lug terminals

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	600 V
Horsepower Rating UL/CSA:	(acc. to UL 200 V) 60 Hp

(acc. to UL 208 V) 60 Hp
(acc. to UL 240 V) 75 Hp
(acc. to UL 480 V) 150 Hp
(acc. to UL 600 V) 200 Hp

Ampere Rating UL/CSA: 200 A

Tightening Torque UL/CSA: 275 in#183;lb

Certificates and Declarations (Document Number)

Declaration of Conformity - CE: [1SCC301131D2705](#)

Environmental Information: [1SCC301149D0202](#)

Instructions and Manuals: [1SCC301031M0213](#)

Container Information

Package Level 1 Units: 1 piece

Package Level 1 Width: 183 mm

Package Level 1 Length: 240 mm

Package Level 1 Height: 95 mm

Package Level 1 Gross Weight: 1.577 kg

Package Level 1 EAN: 6417019232645

Classifications

Object Classification Code: Q

ETIM 5: EC000216 - Switch disconnecter

ETIM 6: EC000216 - Switch disconnecter

