

DESCRIPTION

Diffusion LED SL-6 is a flexible 10mm linear LED strip. Available in lengths of 16 ft or 100ft rolls, it may be cut every 6 LEDs (50mm / 2"). It uses 120 LEDs per Meter (36 LEDs / ft)

FEATURES

- * 3M industrial strength adhesive tape
- * Long Life LED: 50,000 hours
- * Voltage Input: 24VDC
- * Dimmable with dimming power supply
- * 24" leads on both ends of each roll

custom lengths available upon request

SPECIFICATIONS

LED: 14.4 watts/Meter (4.5 watts/ft)
LAMP LIFE: 50,000 hours LM80
POWER INPUT: 24V DC
CRI > 91

LUMENS
2700K = 1220 lm/M (366 lm/ft)
3000K = 1282 lm/M (384 lm/ft)
3400K = 1344 lm/M (402 lm/ft)
4100K = 1400 lm/M (420 lm/ft)



NOTE: SL6 NEEDS TO BE INSTALLED ON ALUM CHANNEL



ORDERING CODE

ORDERING CODE	LENGTH	VOLTAGE	COLOR
SL6-IN	16	24V	2700
SL6-IN	16 ft 100 ft	24 Volt	2700 K 3000 K 3400 K 4100 K

Project: _____
Type: _____
Date: _____
Part #: _____