

SL3—IN DIFFUSION LED STRIP — INDOOR

DESCRIPTION

Diffusion LED SL-3 is a flexible 8mm linear LED strip. Available in lengths of 16 ft or 100ft rolls, it may be cut every 6 LEDs (50mm / 2"). It uses 120 LEDs per Meter (36 LEDs / ft)

FEATURES

- * 3M industrial strength adhesive tape
- * Long life LED: 50,000 hours
- * Voltage Input: 24VDC
- * Dimmable with dimming power supply
- * 24" leads on both ends of each roll

custom lengths available upon request

SPECIFICATIONS

LED: 10 watts/Meter (3 watts/ft)
LAMP LIFE: 50,000 hours LM80
POWER INPUT: 24V DC
CRI > 91

LUMENS

2700K = 788 lm/M (236 lm/ft)
3000K = 832 lm/M (249 lm/ft)
3400K = 876 lm/M (263 lm/ft)
4100K = 908 lm/M (279 Lm/ft)



ORDERING
CODE

LENGTH

VOLTAGE

COLOR

SL3-IN	16	24V	2700
SL3-IN	16 ft 100 ft	24 Volt	2700 K 3000 K 3400 K 4100 K

Project: _____
Type: _____
Date: _____
Part #: _____