



LED General Purpose Floods FL

FL300-NW-G1-T-FL-6-BZ

LED, 300W, 4000K, Wide Flood Optics, Textured Dark Bronze - 113 lm/W

The Philips Keene LED Floodlights offer energy saving LED technology for long life and reduced maintenance. Versatile and stylish with five different sizes to choose from provides application flexibility for ground mount, wall mount, or pole mount installations. Ideal for sign lighting, building facades, security lighting, and general purpose floodlighting applications.

Product data

General Information	
Colour Temperature	4000K
CRI	80
Photometric Distribution Type	NEMA 7H x 7V
Mounting	Surface Ground / Floor Wall
Operating and Electrical	
Luminaire Input Watts	301
Voltages	347 V
Mechanical and Housing	
Shape	Rectangular
Initial Performance (IEC Compliant)	
Luminaire Lumens	34025

Efficacy	113 lm/W
Product Data	
Order product name	FL300-NW-G1-T-FL-6-BZ
Catalog Number	FL300-NW-G1-T-FL-6-BZ
EAN/UPC - Product	783352024244
Order code	912401467980
Catalog Number Description	LED, 300W, 4000K, Wide Flood Optics, Textured Dark Bronze
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912401467980
Net Weight (Piece)	17.200 kg