



AWL-LED26W



The AWL-LED26W is a multi-purpose fixture that can be used to replace wall packs and floods up to 175 watt metal halide. The head can be aimed straight down for dark sky requirements or aimed out to deliver the light where it is required. The AWL-LED26W comes complete with a photocell, available in 120 volts and 347 volts. Standard finish is bronze or white. Ideal for use on building perimeters, loading docks, schools, townhouse complexes and apartment buildings. For a lower wattage version please see AWL-LED14W.

HOUSING Die cast aluminum with a powder coat paint finish. Unit has four conduit entries. Mounts to standard junction box.

DRIVER 120 or 347 volts total power consumed 26.6 watts.

LEDs Two led arrays with six LEDS, 2570 lumens out of the fixture, 5000k., CRI > 70. LEDS operating temperature is -40° C to 40°C.

LENS Clear tempered glass with a gasket.

HARDWARE Tamper proof stainless steel.

FINISH Standard finish is Bronze or White. Please consult factory for custom colour.

PHOTOCELL Included



MOUNTING OPTIONS Wall mount, ceiling mount and ground mounted on a concrete pad or stake.

OPERATING TEMPERATURE -40° C to 40° C.


RATED IP65

WARRANTY 5 YEARS

MEETS LM-79, LM-80

APPROVALS cULus,





Photometric Data

SUMMARY DATA

FILENAME: H114C.IES
IESNA:LM-63-2002
[TEST] H114C
[TESTLAB] Lumentra, Inc.
[MORE] 160 Frobisher Drive, Unit 5
[MORE] Waterloo, Ontario
[MORE] NVLAP LAB CODE 500084

[MORE] Waterloo, Ontario [MORE] NVLAP LAB CODE 500084-0 [ISSUEDATE] 02-04-2014 [MANUFAC] RAB DESIGN LIGHTING INC.

CATALOG NUMBER: AWL-LED26W-120-PC-BRZ

[MORE] TORONTO, ONTARIO [LUMCAT] AWL-LED26W-120-PC-BRZ

[LUMINAIRE] RAB DESIGN EXTERIOR WALL MOUNTED LED LUMINAIRE [MORE] WITH DIFFUSE ALUMINUM REFLECTOR AND CLEAR OUTER LENS [LAMP] ONE WHITE ARRAY LED. LUMEN OUTPUT = 2570 LMS. [OTHER] ABSOLUTE PHOTOMETRY EFFICIENCY (Total):
EFFICIENCY (Down / Up):
EFFICIENCY (Street / House):
LUMENS/LAMP:
NO. OF LAMPS:
LUMINOUS OPENING:
Width:

 LUMINOUS OPENING:
 POINT SOURCE


 Width:
 0.00 (Feet)


 Length:
 0.00

 Height:
 0.00

 INPUT WATTS:
 26.61

ISO-ILLUMINANCE DIAGRAM





- 256868.1 %

0.0 % / 0.0 %

- 256868.1 % / 0.0 %

www.rabdesign.ca