

LED DIMMABLE DRIVERS

ACCENT LED LIGHTING

Dimming is made easy with our LED Dimmable Driver series. These products will allow you to find just the right amount of light based on the time of day your lighting fixtures are being used.







KEY FEATURES

Wide range of wattage options Compatible with all DALS low voltage LED products



MODEL

BT06DIMLED-IC 6W dimmable LED hardwire driver BT12DIMLED-IC 12W dimmable LED hardwire driver BT24DIMLED-IC 24W dimmable LED hardwire driver BT36DIMLED 36W dimmable LED hardwire driver **BT48DIMLED** 48W dimmable LED hardwire driver

SPECIFICATIONS


- Constant voltage mode power supply.
- AC-dimming supply (with TRIAC or ELV dimmer).
- Protection: short circuit / Over voltage.
- Integrated junction box for hard wire installation.
- Fully isolated metal case Cooling by air convection.
- 2 years warranty.
- ETL certification.
- Optimal dimming when used at 50% or more of total load.
- Input voltage: 100VAC-230VAC, 50/60Hz.
- Output voltage: 12V DC. • Load Range: 50% to 100%.
- Operating temperature: -30°C to 45°C.


INSTALLATION


- Standard knockout 1/2".
- Damp location rated.


FINISH


GR Grey











ORDERING EXAMPLE

BT06DIMLED-IC

Would order a 6W dimmable LED hardwire driver.